



600 °C Series



Platinum temperature sensor with wires

For high temperatures




Benefits & characteristics

- Excellent long-term stability
- Low self-heating
- Fast response time
- Small dimensions
- Vibration and temperature shock resistant
- Paired sensors available
- 1/5 IEC and 1/10 IEC available
- Customer-specific sensor available upon request



Illustration ¹⁾



¹⁾ for actual size see dimensions in order information

H = Substrate Height

H2 = Height

W = Width

L = Length

L_w = Wire length

Dimension tolerances:

W ±0.2 mm, L ±0.2 mm, H ±0.1 mm, H2 ±0.3 mm,

L_w (up to 30 mm) ±1 mm



Technical Data

Operating temperature range:	-200 °C to +600 °C	
Nominal resistance:*	100 Ω at 0 °C	
	100 Ω at 0 °C	
	500 Ω at 0 °C	
	1000 Ω at 0 °C	
	2000 Ω at 0 °C	
Characteristics curve:*	3850 ppm/K	
Long-term stability:	< 0.04 % at 1000 h at maximal operating temperature	
Tolerance class: * (dependent on temperature range)	iST reference	
	IEC 60751 F0.15	A
	IEC 60751 F0.3	B
	IEC 60751 F0.6	C
	IEC 60751 F0.1	Y
Connection:*	Pt-cladded Ni-wire, Ø 0.2 mm (solderable, weldable, crimpable, brazeable)	
Design:	ESD optimized ²⁾	
Alternative wire construction:*	Inverted wired	
Recommended applied current: ¹⁾	1 mA at 100 Ω	
¹⁾ Self-heating must be considered	0.6 mA at 200 Ω	
	0.5 mA at 500 Ω	
	0.3 mA at 1000 Ω	
	0.2 mA at 2000 Ω	
Other alternatives: *	<ul style="list-style-type: none"> ▪ Housed in round ceramics (for dry environments only) - See data sheet DTP_Round_Housing_E ▪ Grouped and paired ▪ Substrate thickness 	

* Customer-specific alternatives available



Order Information



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
----------------------------	------	---	--------	------------	------------------------------------	-------------------	---------

6W (Pt-cladded Ni-wire, Ø 0.2 mm)

100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	101371	P0K1.161.6W.Y.007	7	
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	100945	P0K1.161.6W.A.007	7	
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	100946	P0K1.161.6W.B.007	7	
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	155582	P0K1.161.6W.Y.010	10	²⁾ ESD optimized
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	154366	P0K1.161.6W.A.010	10	²⁾ ESD optimized
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	154367	P0K1.161.6W.B.010	10	²⁾ ESD optimized
500 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	100219	P0K5.161.6W.Y.010	10	
500 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	100218	P0K5.161.6W.A.010	10	
500 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	100217	P0K5.161.6W.B.010	10	
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	100247	P1K0.161.6W.Y.010	10	
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	100246	P1K0.161.6W.A.010	10	
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	100245	P1K0.161.6W.B.010	10	
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	153442	P0K1.202.6W.Y.007	7	²⁾ ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.15 (class A)	153741	P0K1.202.6W.A.007	7	²⁾ ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	153742	P0K1.202.6W.B.007	7	²⁾ ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	155716	P0K1.202.6W.B.007.S	7	Packaged in blister of 500 pcs
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	155762	P0K1.202.6W.Y.010	10	²⁾ ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.15 (class A)	155763	P0K1.202.6W.A.010	10	²⁾ ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	155764	P0K1.202.6W.B.010	10	²⁾ ESD optimized
500 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	On request	P0K5.202.6W.Y.007	7	
500 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.15 (class A)	On request	P0K5.202.6W.A.007	7	
500 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	101108	P0K5.202.6W.B.007	7	
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	155770	P1K0.202.6W.Y.007	7	²⁾ ESD optimized
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.15 (class A)	154721	P1K0.202.6W.A.007	7	²⁾ ESD optimized
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	155771	P1K0.202.6W.B.007	7	²⁾ ESD optimized
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	155774	P1K0.202.6W.Y.010	10	²⁾ ESD optimized
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.15 (class A)	155773	P1K0.202.6W.A.010	10	²⁾ ESD optimized
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	155772	P1K0.202.6W.B.010	10	²⁾ ESD optimized



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	101401	P0K1.216.6W.Y.007	7	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100589	P0K1.216.6W.A.007 P	7	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100599	P0K1.216.6W.B.007	7	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	100429	P0K1.216.6W.Y.010	10	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100414	P0K1.216.6W.A.010	10	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100419	P0K1.216.6W.B.010	10	
1000 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	101042	P1K0.216.6W.Y.010	10	
1000 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100588	P1K0.216.6W.A.010	10	
1000 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100552	P1K0.216.6W.B.010	10	
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	100579	P0K1.232.6W.Y.007	7	
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	152671	P0K1.232.6W.A.007	7	²⁾ ESD optimized
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	152672	P0K1.232.6W.B.007	7	²⁾ ESD optimized
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	154005	P0K1.232.6W.Y.010	10	²⁾ ESD optimized
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	154004	P0K1.232.6W.A.010	10	²⁾ ESD optimized
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	154000	P0K1.232.6W.B.010	10	²⁾ ESD optimized
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	101357	P0K1.232.6W.Y.020	20	
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	101356	P0K1.232.6W.A.020	20	
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100875	P0K1.232.6W.B.020	20	
500 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	100223	P0K5.232.6W.Y.010	10	
500 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	100222	P0K5.232.6W.A.010	10	
500 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100221	P0K5.232.6W.B.010	10	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	100545	P1K0.232.6W.Y.007	7	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	100830	P1K0.232.6W.A.007	7	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100546	P1K0.232.6W.B.007	7	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	153765	P1K0.232.6W.Y.010	10	²⁾ ESD optimized
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	153766	P1K0.232.6W.A.010	10	²⁾ ESD optimized
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	153768	P1K0.232.6W.B.010	10	²⁾ ESD optimized
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	On request	P1K0.232.6W.Y.020	20	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	151322	P1K0.232.6W.A.020	20	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100550	P1K0.232.6W.B.020	20	



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
200 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K2.420.6W.Y.010	10	
200 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	On request	P0K2.420.6W.A.010	10	
200 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	104300	P0K2.420.6W.B.010	10	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.420.6W.Y.007	7	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	101077	P1K0.420.6W.A.007	7	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	101093	P1K0.420.6W.B.007	7	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.420.6W.Y.010	10	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	101288	P1K0.420.6W.A.010	10	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	101129	P1K0.420.6W.B.010	10	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K1.516.6W.Y.007	7	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100835	P0K1.516.6W.A.007	7	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100836	P0K1.516.6W.B.007	7	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	100148	P0K1.516.6W.Y.010	10	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100147	P0K1.516.6W.A.010	10	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100146	P0K1.516.6W.B.010	10	
500 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	100229	P0K5.516.6W.Y.010	10	
500 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100228	P0K5.516.6W.A.010	10	
500 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100227	P0K5.516.6W.B.010	10	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.516.6W.Y.007	7	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100828	P1K0.516.6W.A.007	7	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100829	P1K0.516.6W.B.007	7	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	100270	P1K0.516.6W.Y.010	10	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100269	P1K0.516.6W.A.010	10	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100268	P1K0.516.6W.B.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100165	P0K1.520.6W.Y.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100163	P0K1.520.6W.A.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100162	P0K1.520.6W.B.010	10	
500 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100235	P0K5.520.6W.Y.010	10	
500 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100234	P0K5.520.6W.A.010	10	
500 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100233	P0K5.520.6W.B.010	10	



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
1000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	156115	P1K0.520.6W.Y.010	10	²⁾ ESD optimized
1000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	156116	P1K0.520.6W.A.010	10	²⁾ ESD optimized
1000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	156117	P1K0.520.6W.B.010	10	²⁾ ESD optimized
2000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P2K0.520.6W.Y.010	10	
2000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	On request	P2K0.520.6W.A.010	10	
2000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100322	P2K0.520.6W.B.010	10	
100 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K1.538.6W.Y.010	10	
100 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.15 (class A)	100785	P0K1.538.6W.A.010	10	
100 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.3 (class B)	100541	P0K1.538.6W.B.010	10	
1000 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.538.6W.Y.010	10	
1000 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.15 (class A)	On request	P1K0.538.6W.A.010	10	
1000 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.3 (class B)	100336	P1K0.538.6W.B.010	10	
1000 Ω	505	5.0 x 5.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.505.6W.Y.010	10	
1000 Ω	505	5.0 x 5.0 x 0.65 / 1.3	F0.15 (class A)	On request	P1K0.505.6W.A.010	10	
1000 Ω	505	5.0 x 5.0 x 0.65 / 1.3	F0.3 (class B)	101208	P1K0.505.6W.B.010	10	
100 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100202	P0K1.102.6W.Y.010	10	
100 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100201	P0K1.102.6W.A.010	10	
100 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100200	P0K1.102.6W.B.010	10	
500 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K5.102.6W.Y.010	10	
500 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100238	P0K5.102.6W.A.010	10	
500 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100237	P0K5.102.6W.B.010	10	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.102.6W.Y.007	7	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	On request	P1K0.102.6W.A.007	7	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100474	P1K0.102.6W.B.007	7	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100308	P1K0.102.6W.Y.010	10	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100473	P1K0.102.6W.A.010	10	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100307	P1K0.102.6W.B.010	10	



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
----------------------------	------	---	--------	------------	------------------------------------	-------------------	---------

6W (Pt-cladded Ni-wire, Ø 0.2 mm, bent 90°), inverted wires

100 Ω	232	2.3 x 2.0 x 1.1	F0.15 (class A)	101143	P0K1.232.6W.A.010.U.S	10	inverted wires
100 Ω	232	2.3 x 2.0 x 1.1	F0.3 (class B)	100975	P0K1.232.6W.B.010.U.S	10	inverted wires

PU (TCR = 3750 ppm/K)

100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100260	PU1K0.232.6W.B.010	10	
-------	-----	------------------------	----------------	--------	--------------------	----	--

6W (Pt-cladded Ni-wire, Ø 0.2 mm), D (substrate thickness, 0.4 mm)

100 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.1 (class Y)	On request	P0K1.232.6W.Y.010.D	10	substrate thickness 4 mm
100 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.15 (class A)	100463	P0K1.232.6W.A.010.D	10	substrate thickness 4 mm
100 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.3 (class B)	100462	P0K1.232.6W.B.010.D	10	substrate thickness 4 mm
1000 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.1 (class Y)	On request	P0K1.232.6W.Y.010.D.S	10	substrate thickness 4 mm
1000 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.15 (class A)	On request	P0K1.232.6W.A.010.D.S	10	substrate thickness 4 mm
1000 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.3 (class B)	154038	P0K1.232.6W.B.010.D.S	10	substrate thickness 4 mm
100 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.1 (class Y)	On request	P0K1.516.6W.Y.010.D	10	substrate thickness 4 mm
100 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.15 (class A)	100334	P0K1.516.6W.A.010.D	10	substrate thickness 4 mm
100 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.3 (class B)	100333	P0K1.516.6W.B.010.D	10	substrate thickness 4 mm
1000 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.1 (class Y)	100340	P1K0.516.6W.Y.010.D	10	substrate thickness 4 mm
1000 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.15 (class A)	100442	P1K0.516.6W.A.010.D	10	substrate thickness 4 mm
1000 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.3 (class B)	100339	P1K0.516.6W.B.010.D	10	substrate thickness 4 mm
100 Ω	520	5.0 x 2.0 x 0.4 / 1.05	F0.1 (class Y)	On request	P0K1.520.6W.Y.010.D	10	substrate thickness 4 mm
100 Ω	520	5.0 x 2.0 x 0.4 / 1.05	F0.15 (class A)	100169	P0K1.520.6W.A.010.D	10	substrate thickness 4 mm
100 Ω	520	5.0 x 2.0 x 0.4 / 1.05	F0.3 (class B)	100167	P0K1.520.6W.B.010.D	10	substrate thickness 4 mm
100 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.1 (class Y)	On request	P0K1.102.6W.Y.010.D	10	substrate thickness 4 mm
100 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.15 (class A)	100855	P0K1.102.6W.A.010.D	10	substrate thickness 4 mm
100 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.3 (class B)	100337	P0K1.102.6W.B.010.D	10	substrate thickness 4 mm
1000 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.1 (class Y)	On request	P1K0.102.6W.Y.010.D	10	substrate thickness 4 mm
1000 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.15 (class A)	100310	P1K0.102.6W.A.010.D	10	substrate thickness 4 mm
1000 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.3 (class B)	100309	P1K0.102.6W.B.010.D	10	substrate thickness 4 mm



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
----------------------------	------	---	--------	------------	------------------------------------	-------------------	---------

6W (Pt-cladded Ni-wire, Ø 0.2 mm), T (substrate thickness, 0.25 mm)

100 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.1 (class Y)	100121	P0K1.232.6W.Y.010.T	10	substrate thickness 0.25 mm
100 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.15 (class A)	100120	P0K1.232.6W.A.010.T	10	substrate thickness 0.25 mm
100 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.3 (class B)	100119	P0K1.232.6W.B.010.T	10	substrate thickness 0.25 mm
1000 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.1 (class Y)	On request	P1K0.232.6W.Y.007.T	7	substrate thickness 0.25 mm
1000 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.15 (class A)	101593	P1K0.232.6W.A.007.T	7	substrate thickness 0.25 mm
1000 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.3 (class B)	101586	P1K0.232.6W.B.007.T	7	substrate thickness 0.25 mm

7W³⁾ (Pt-wire, Ø 0.2 mm), D (substrate thickness, 0.4 mm)

200 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.1 (class Y)	On request	P0K2.516.7W.Y.007.D	7	substrate thickness 4 mm
200 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.15 (class A)	150635	P0K2.516.7W.A.007.D	7	substrate thickness 4 mm
200 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.3 (class B)	100880	P0K2.516.7W.B.007.D	7	substrate thickness 4 mm

³⁾ Operating temperature range of -200 °C to +600 °C

7W³⁾ (Pt-wire, Ø 0.2 mm, (161) (232) (520) / Ø 0.15 mm (308))

100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	On request	P0K1.161.7W.Y.010	10	substrate thickness 0.25 mm
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	100465	P0K1.161.7W.A.010	10	substrate thickness 0.25 mm
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	100446	P0K1.161.7W.B.010	10	substrate thickness 0.25 mm
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100895	P0K1.232.7W.Y.010	10	
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100511	P0K1.232.7W.A.010	10	
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100341	P0K1.232.7W.B.010	10	
100 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.1 (class Y)	100561	P0K1.308.7W.Y.007	7	substrate thickness 0.25 mm
100 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.15 (class A)	100537	P0K1.308.7W.A.007	7	substrate thickness 0.25 mm
100 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.3 (class B)	100538	P0K1.308.7W.B.007	7	substrate thickness 0.25 mm
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K1.520.7W.A.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	On request	P0K1.520.7W.A.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100170	P0K1.520.7W.B.010	10	



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
7W ⁴⁾ (Pt-wire, Ø 0.15 mm)							
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	On request	P1K0.161.7W.Y.007	7	substrate thickness 0.25 mm
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	101114	P1K0.161.7W.A.007	7	substrate thickness 0.25 mm
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	101115	P1K0.161.7W.B.007	7	substrate thickness 0.25 mm
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	On request	P1K0.161.7W.Y.010	10	substrate thickness 0.25 mm
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	100757	P1K0.161.7W.A.010	10	substrate thickness 0.25 mm
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	100759	P1K0.161.7W.B.010	10	substrate thickness 0.25 mm
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.232.7W.Y.010	10	
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100766	P1K0.232.7W.A.010	10	
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100258	P1K0.232.7W.B.010	10	
100 Ω	308	3.0 x 0.8 x 0.25 / 0.6	1/10 F0.3 (class K) ⁵⁾	100969	P0K1.308.7W.K.007	7	substrate thickness 0.25 mm
1000 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.1 (class Y)	100725	P1K0.308.7W.Y.007	7	substrate thickness 0.25 mm
1000 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.15 (class A)	100514	P1K0.308.7W.A.007	7	substrate thickness 0.25 mm
1000 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.3 (class B)	100432	P1K0.308.7W.B.007	7	substrate thickness 0.25 mm

⁴⁾ Operating temperature range of -200 °C to +600 °C

⁵⁾ 1/10 IEC 60751 in the range of +15 °C to +35 °C

Additional documents

Application note

Document name:

ATP_E



Order Information

Platinum Sensor - Secondary reference



Material

P = Platinum

TCR

= Pt 3850 ppm/K	G = Pt 3911 ppm/K
U = Pt 3750 ppm/K	W = Pt 3850 ppm/K (extended operating temperature range in class A)

Resistance in Ω at 0°C

Size in mm

Operating temperature range

1 = -50 °C to + 150 °C	6 = -200 °C to + 600 °C
2 = -50 °C to + 200 °C	7 = -200 °C to + 750 °C
3 = -200 °C to + 300 °C	8 = -200 °C to + 850 °C
4 = -200 °C to + 400 °C	10 = -70 °C to + 1000 °C

Connections

S = SIL	FK = Flat wire customer specific
I = Insulated wire	SW = Perpendicular wire
K = Extended wire	L = Insulated stranded wire
W = Wire	E = Enameled Cu-wire
FW = Flat wire	SE = Perpendicular enamelled Cu-wire

Tolerance class

A = IEC 60751 F0.15	K = Customer-specific
B = IEC 60751 F0.3	P = Pair
C = IEC 60751 F0.6	G = Group
Y = IEC 60751 F0.1	

Wire length in mm

Special

T = Substrate thickness 0.25 mm	M = Metallized backside
D = Substrate thickness 0.38 mm	U = Inverted welding
R = Round housing	S = Special
W = Sintered powder	

P OK1. 520. 6 W. A. 007. D



Innovative Sensor Technology IST AG • Stegrütistrasse 14 • 9642 Ebnat-Kappel • Switzerland
+41 71 992 01 00 • info@ist-ag.com • www.ist-ag.com

Technical specifications are subject to change without prior notice. The information contained in this data sheet has been carefully reviewed and is believed to be accurate; however, no liability is assumed for any errors or omissions. Continuous exposure to extreme operating conditions may impact product lifetime or reliability. The customer is solely responsible for assessing the suitability and fitness of the product for their specific application. This product is not designed, authorized, or warranted for use in life support or safety-critical applications. The customer agrees to hold the supplier harmless from any claims, damages, or liabilities arising from such use. No explicit or implied warranties, including but not limited to warranties of merchantability or fitness for a particular purpose, are provided. The material provided herein may not be reproduced, adapted, merged, translated, stored, or utilized in any form without prior written consent from the copyright holder. No transfer of any intellectual property rights is granted or implied. All rights reserved.